

## Industrial process automation meets easy operation

- Innovative software „SIA“
- Intuitive operation via tablet
- Control via symbols & gestures, graphical visualisation
- No previous knowledge necessary for the operator
- Setup process possible without programmer
- Quick & easy changeover
- Easy maintenance thanks to modular inserts & maintenance door
- Precise setup using live image
- Worldwide support by qualified staff
- Short delivery time
- Continuous software development & regular updates

### Technical description:

- Precise pulse or spray dosing of various fluids & pastes
- Intuitive setup and operation using „SIA“ software via Tablet
- Precise definition of the processing points thanks to camera support
- Manual component feeding and removal

### Applications areas:

- Pre & small series
- Laboratory testing & prototyping
- Seasonal operations
- AfterSales (spare & wear parts)
- Universities & Institutes

## SMART SOLUTIONS DISPENSE



## Technical data

<b>Cell size (including rollers):</b>	1000 x 1000 x 2200 mm
<b>Article weight:</b>	< 5 kg
<b>Article dimensions:</b>	< 200 x 200 x 200 mm
<b>Movement range X,Y-table:</b>	200 x 300 mm
<b>Z-stroke:</b>	200 mm
<b>Pulse frequency:</b>	60 Hz
<b>Dosing functions:</b>	Pulse dosing, spray dosing
<b>Electrical connection:</b>	CEE plug 400 - 480 V, 50 - 60 Hz, 16 A
<b>Safety:</b>	Safety camera in the operating area
<b>Maintenance:</b>	Maintenance rear door incl. safety contact
<b>Switch cabinet:</b>	Module inserts under the table

